

Specification Sheet

Part Number: 156-02462



Versatile and robust fir tree design provides low insertion effort yet delivers exceptional retention strength in an 8 mm hole and M10 threaded hole.

Wider and thinner strap design increases flexibility and minimizes pinching of bundles, hoses and tubing.

PA46 nylon material provides great performance at up to 135°F continuous operating temperature.

2-Piece Cable Tie/Fir Tree Mount, 8mm Hole and M10 Threaded Hole, PA66HIRHSUV, BK, 1200/ctn

Article Number	156-02462
Type	WSSDFTM10WSSDSET
Color	Black (BK)
Quantity Per	bag
Product Description	These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.
Short Description	2-Piece Cable Tie/Fir Tree Mount, 8mm Hole and M10 Threaded Hole, PA66HIRHSUV, BK, 1200/ctn

Global Part Name	WSSDFTM10WSSDSET-PA66HIRHSUV-BK
------------------	---------------------------------

Minimum Tensile Strength (Imperial)	120.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	533
-----------------------------------	-----

Length L (Imperial)	9.1
---------------------	-----

Length L (Metric)	231.14
-------------------	--------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.88
--------------------	------

Width W (Metric)	22.6
------------------	------

Bundle Diameter Min (Imperial)	0.37
--------------------------------	------

Bundle Diameter Min (Metric)	9.4
------------------------------	-----

Bundle Diameter Max (Imperial)	2.25
--------------------------------	------

Bundle Diameter Max (Metric)	57.15
------------------------------	-------

Height H (Imperial)	0.98
Height H (Metric)	23.7
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.23
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.3 - 0.33
Mounting Hole Diameter D (Metric)	7.6 - 8.4 mm M10 Threaded
Mounting Hole Diameter D Min (Imperial)	0.3
Mounting Hole Diameter D Max (Imperial)	0.33
Mounting Hole Diameter D Max (Metric)	8.4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1200
Package Quantity (Metric)	1200
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02462](#)