

Specification Sheet

Part Number: 157-00460



Low-Profile head allows mounts to stack, providing more mounting versatility from a single stud.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

1-Pc Low Profile M5/M6 Stud Mount Tie, 8.2" Tie, 80lb Tensile Strength, PA66HIRHSUV, Black, 2500/ctn

Article Number 157-00460

Type T80ROSLPSB5-6U

Color Black (BK)

Quantity Per carton

Product Description One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description 1-Pc Low Profile M5/M6 Stud Mount Tie, 8.2" Tie, 80lb Tensile Strength, PA66HIRHSUV, Black, 2500/ctn

Global Part Name T80ROSLPSB5-6U-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	80.0
Minimum Tensile Strength (Metric)	355
Length L (Imperial)	8.2
Length L (Metric)	208.3
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.56
Width W (Metric)	14.22
Bundle Diameter Min (Imperial)	0.14
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00460
Height H (Imperial)	0.25

Height H (Metric)	6.30
Mounting Hole Diameter D (Imperial)	0.24 x 0.04 "; 0.2 x 0.03
Mounting Hole Diameter D (Metric)	T6 M5 x 0.8 M6 x 1 T5
Mounting Hole Diameter D Min (Imperial)	0.2
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.0
Stud Diameter (Metric)	5.0 mm 6.0 mm
Stud Diameter (Imperial)	0.20 ", 0.24
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00460](#)