

Specification Sheet

Part Number: 2FRP9M



Sheathing allows flexible routing and lead-out of cables
The inner edges are beveled preventing damage to cables
Sheathing is reusable and resistant to most chemicals
Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.25" Diameter, PE-FR, Natural, 1000ft/roll

Article Number 161-05031

Type 2FRP

Color Natural (NA)

Quantity Per reel

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Suitable for applications requiring a self-extinguishing material. Lower cost than polyamide 6 or Teflon materials. Natural color is milky white.

Short Description Spiralwrap Protective Sheathing, 0.25" Diameter, PE-FR, Natural, 1000ft/roll

Global Part Name 2FRP-PE-FR-NA

Length L (Imperial) 1000.0

Length L (Metric) 304.8

Variant Spiral Binding

Bundle Diameter Min (Imperial) 0.18

Bundle Diameter Min (Metric) 4.75

Bundle Diameter Max (Imperial) 2.0

Bundle Diameter Max (Metric) 50.8

Diameter D (Imperial) 0.25

Diameter D (Metric) 4.1

Nominal Diameter (Imperial) 0.25

Nominal Diameter (Metric) 6.35

Wall Thickness WT (Imperial) .045

Wall Thickness WT (Metric) 1.14

Material	Polyethylene, flame retardant (PE-FR)
Material Shortcut	PE-FR
Flammability	UL 94 V-2
Operating Temperature	-4°F to +176°F (-20°C to +80°C)
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	304.8
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[2FRP9M](#)