

## Specification Sheet

Part Number: 161-66100



Industry standard blue color assists with visual detection and reduces the risk of contamination.

Included applicator tool makes installation fast and easy.

High stainless-steel content is both detectable and corrosion resistant.

Open design accommodates breakouts at any point along the bundle.

**Article Number** 161-66100

**Type** HWPPMC16

**Color** Blue (BU)

**Quantity Per** box

**Product Description** Helawrap HWPPMC provides flexible, durable cable and hose protection. It is ideal for food-processing machines and related environments. Protects against abrasion, making it appropriate for applications where movement is an issue. Helawrap is quick and easy to use, making it ideal for installation and maintenance operations.

**Short Description** Helawrap Metal-Content, HWPPMC16, .63" Dia, PP/SS, Blue, 82 ft/roll

<b>Global Part Name</b>	HWPPMC16-PP/SS-BU
<b>Variant</b>	Spiral Binding
<b>Bundle Diameter Min (Imperial)</b>	0.51
<b>Bundle Diameter Min (Metric)</b>	13
<b>Bundle Diameter Max (Imperial)</b>	0.63
<b>Bundle Diameter Max (Metric)</b>	16
<b>Nominal Diameter (Imperial)</b>	0.63
<b>Nominal Diameter (Metric)</b>	16
<b>Wall Thickness WT (Imperial)</b>	0.030
<b>Wall Thickness WT (Metric)</b>	0.80
<b>Material</b>	Stainless Steel (SS) Polypropylene (PP)
<b>Material Shortcut</b>	PP SS
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes

**Operating Temperature** -76°F to +212°F (-60°C to +100°C)

**Reach Compliant (Article 33)** Yes

**ROHS Compliant** Yes

**Package Quantity (Imperial)** 82.0

**Package Quantity (Metric)** 25

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[161-66100](#)