

## Specification Sheet

Part Number: B-M25-M20



Quickly reduces metallic metric threads for use with metric threaded entries.

Achieve IP68 level ingress protection with use of sealing washer.

Metallic Thread Converter, M25 External Thread and M20 Internal Thread, NPB Metal, 10/pkg

<b>Article Number</b>	166-50215
<b>Type</b>	B-M25-M20
<b>Color</b>	Metal (ML)
<b>Quantity Per</b>	pack
<b>Product Description</b>	Nickel plated brass thread converter. Metric internal threads and metric external threads.
<b>Short Description</b>	Metallic Thread Converter, M25 External Thread and M20 Internal Thread, NPB Metal, 10/pkg
<b>Global Part Name</b>	B-M25-M20-NPB-ML

**Length L (Imperial)** 0.57

**Length L (Metric)** 14.5

**Variant** Converter

**Height H (Imperial)** 1.14

**Height H (Metric)** 29.0

**Nominal Diameter (Metric)** 25

**Material** Nickel Plated Brass (NPB)

**Material Shortcut** NPB

**Operating Temperature** -58°F to +572°F (-50°C to +300°C)

**Package Quantity (Imperial)** 10

**Package Quantity (Metric)** 10

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[B-M25-M20](#)