

Specification Sheet

Part Number: 166-90293

Material is easy to use and cut; reduces installation time and labor costs. Flexible, abrasion resistant and durable for a variety of applications.

Good impact strength; recovers quickly if crushed.

UV resistant; suitable for use in outdoor applications.

Offered in fine or coarse corrugated pitch.



HelaGuard Non-Metallic Conduit, Std. Weight, 1.25" Dia, Nylon PA6, Black, 82 ft/reel

Article Number 166-90293

Type HG-SW1250

Color Black (BK)

Quantity Per reel

Product Description A standard-weight corrugated conduit made of PA6 nylon that offers flexible abrasion protection for wire and cable bundles. Easy to cut and use, the material is highly resistant to solvents and oils. Combine with HelaGuard non-metallic fittings for IP66 rating or greater protection against water, wind and dirt.

Short Description HelaGuard Non-Metallic Conduit, Std. Weight, 1.25" Dia, Nylon PA6, Black, 82 ft/reel

Global Part Name HG-SW1250-PA6-BK

Length L (Imperial) 82.0

Length L (Metric) 25.0

Material Polyamide 6 (PA6)

Material Shortcut PA6

Operating Temperature -40°F to +248°F (-40°C to +120°C)

ROHS Compliant Yes

Package Quantity (Imperial) 82

Package Quantity (Metric) 25.0

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90293](#)