

Specification Sheet

Part Number: 166-90356



Nickel plated brass thread ensures secure connection with brass plated or nylon fittings.

NPT thread pattern works with metallic or non-metallic threaded fittings.

Use NPT metallic locknuts with 1.25", 1.5" and 2" nylon fittings.

HelaGuard Metallic Locknuts, 3/4" NPT Thread, 0.75" Dia., NPB Metal, 10/pkg

Article Number	166-90356
Type	ALNPB-0750
Color	Metal (ML)
Quantity Per	bag
Product Description	Locknuts work with NPT threaded fittings or knockout entries.
Short Description	HelaGuard Metallic Locknuts, 3/4" NPT Thread, 0.75" Dia., NPB Metal, 10/pkg
Global Part Name	ALNPB-0750-NPB-ML

Material	Nickel Plated Brass (NPB)
Material Shortcut	NPB
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	7415338550

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90356](#)