

Specification Sheet

Part Number: 166-90506

External NPT thread provides a secure connection.

Twist-on installation makes future access fast and easy.

Internal spigot design helps ease threading of fitting onto conduit.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP65 rating for protection against wind, dirt and low pressure jets of water from all directions.



HelaGuard Non-Metallic IP65 Compression Fitting, Straight, NPT Thread, 2.0" Dia., Black, 1/pkg

Article Number 166-90506

Type PSR200-S-2000

Color Black (BK)

Quantity Per pack

Product Description Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.

Short Description	HelaGuard Non-Metallic IP65 Compression Fitting, Straight, NPT Thread, 2.0" Dia., Black, 1/pkg
Global Part Name	PSR200-S-2000-PA66-BK
Length L (Imperial)	2.2
Length L (Metric)	56.0
Outside Diameter OD (Imperial)	2.99
Outside Diameter OD (Metric)	76.0
Nominal Diameter (Imperial)	2.5
Nominal Diameter (Metric)	63
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1

Package Quantity (Metric) 1

Customs Number 3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[166-90506](#)