

Specification Sheet

Part Number: CTP10UNSLIT

Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture

Tubing protects cables and wires against automotive fluids, vibration wear

Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight

Nylon material is formulated to withstand high temperatures



Convolute Tubing, Unslit, 1.0" Dia, PE, Black, 1800 ft/ctn

Article Number	169-60536
Type	CTP10UNSLIT
Color	Black (BK)
Quantity Per	carton

Product Description HellermannTyton's Convolute Tubing, also known as Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It can also serve to protect valuable hoses and cables. Convolute tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Short Description Convolute Tubing, Unslit, 1.0" Dia, PE, Black, 1800 ft/ctn

Global Part Name CTP10UNSLIT-PE-BK

Length L (Imperial) 300.0

Length L (Metric) 91.4

Variant Unslit

Inner Diameter D (Imperial) 1.069

Inner Diameter D (Metric) 27.16

Diameter D (Imperial) 1.304

Diameter D (Metric) 33.13

Outside Diameter OD (Imperial) 1.304

Outside Diameter OD (Metric) 33.13

Nominal Diameter (Imperial) 1

Nominal Diameter (Metric) 25.4

Wall Thickness WT (Imperial) 0.006

Wall Thickness WT (Metric) 0.152

Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Not flame retardant
Halogen Free	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1800
Package Quantity (Metric)	548.64

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTP10UNSLIT](#)