

Specification Sheet

Part Number: 170-03231



Self-wrapping feature allows easy installation and future access to wire and cables.

Unique blend and construction using monofilament and multifilament strands provide flexibility, high coverage and abrasion resistance.

Extra overlapping design keeps wires contained even in tight bend conditions.

Braided Sleeving, Woven Convoluted Wrap, 3/16" Dia, PET, Orange, 500.0 ft/reel

| | |
|---------------------|---|
| Article Number | 170-03231 |
| Type | BSPW316 |
| Color | Orange (OG) |
| Quantity Per | reel |
| Product Description | Split Wrap Woven Sleeving is a self-closing sleeving manufactured from a unique blend of monofilament and multifilament polyester fibers that resemble a tightly woven material. The wrap around design provides increased flexibility, better coverage and greater resistance from abrasion for wires, cables and assemblies. Can also be used to reduce noise in applications that involve movement, while protecting sensitive electronics and communication systems from dust and debris. |
| Short Description | Braided Sleeving, Woven Convoluted Wrap, 3/16" Dia, PET, Orange, 500.0 ft/reel |

| | |
|------------------|----------------|
| Global Part Name | BSPW316-PET-OG |
|------------------|----------------|

| | |
|---------------------|-------|
| Length L (Imperial) | 500.0 |
|---------------------|-------|

| | |
|-------------------|-------|
| Length L (Metric) | 152.4 |
|-------------------|-------|

| | |
|--------------------------------|-------|
| Bundle Diameter Min (Imperial) | 0.098 |
|--------------------------------|-------|

| | |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 2.5 |
|------------------------------|-----|

| | |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 0.19 |
|--------------------------------|------|

| | |
|------------------------------|-----|
| Bundle Diameter Max (Metric) | 4.7 |
|------------------------------|-----|

| | |
|-----------------------|-------|
| Diameter D (Imperial) | 0.188 |
|-----------------------|-------|

| | |
|---------------------|-----|
| Diameter D (Metric) | 5.0 |
|---------------------|-----|

| | |
|-----------------------------|-------|
| Nominal Diameter (Imperial) | 0.197 |
|-----------------------------|-------|

| | |
|---------------------------|-----|
| Nominal Diameter (Metric) | 5.0 |
|---------------------------|-----|

| | |
|------------------------------|-------|
| Wall Thickness WT (Imperial) | 0.027 |
|------------------------------|-------|

| | |
|----------------------------|-----|
| Wall Thickness WT (Metric) | 0.7 |
|----------------------------|-----|

| | |
|----------|-----------------|
| Material | Polyester (PET) |
|----------|-----------------|

| | |
|-------------------|-----|
| Material Shortcut | PET |
|-------------------|-----|

| | |
|------------------------------|-----------------------------------|
| Flammability | FMVSS 302 UL 94 V-0 |
| Halogen Free | No |
| UV Resistant (Yes/No) | No |
| Operating Temperature | -94°F to +302°F (-70°C to +150°C) |
| Reach Compliant (Article 33) | No |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 152.4 |
| Customs Number | 5806322000 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03231](#)