

## Specification Sheet

Part Number: TSRPI-RB

Pre-scored knockouts on the base and all four sides remove easily to accomodate 0.5", 0.75" or 1.0" diameter conduit and all HellermannTyton TSR/TSRP raceway sizes.

Simple two piece design is easy to install and includes foam tape backing with rubber based adhesive to assist with temporary positioning and mounting.

Accommodates a variety of alarm/detector and fixture makes and models.

PVC construction is lightweight and durable.

Covers are designed to overlap raceway mating points to hide uneven cuts.

Fittings incorporate a minimum 1" bend radius per TIA/EIA 568-B and 569-A standards.

UL 5A Listed to 600V and CSA Certified to 300V (not to exceed 10 lbs. per UL and 5 lbs. per CSA.)



Round Junction Box, 1-1/4" Deep, PVC, Ivory, 1/bg

Article Number 250-00212

Type TSRPI-RB

Color Ivory (IV)

Quantity Per EA

|                     |   |
|---------------------|---|
| Product Description | Designed for mounting of low and line voltage fixtures such as hanging lights, smoke detectors, carbon monoxide detectors and security cameras, the TSRP round junction box complements HellermannTyton's full line of power rated TSRP and low voltage TSR raceway systems. The TSRP round junction box is constructed of a durable PVC material and is available in white, office white and ivory to coordinate with all HellermannTyton surface mount raceway systems. |
| Short Description   | Round Junction Box, 1-1/4" Deep, PVC, Ivory, 1/bg   |
| Global Part Name    | TSRPI-RB-PVC-BGE  |
| Length L (Imperial) | 5.25  |
| Length L (Metric)   | 133.35  |
| Width W (Imperial)  | 5.25  |
| Width W (Metric)    | 133.35  |
| Height H (Imperial) | 1.25  |
| Height H (Metric)   | 31.75   |
| Material            | Polyvinylchloride (PVC)   |
| Material Shortcut   | PVC   |
| Flammability        | UL 94 V-0   |
| Halogen Free        | No  |

|                              |                |
|------------------------------|----------------|
| UV Resistant (Yes/No)        | No             |
| Operating Temperature        | +122°F (+50°C) |
| Reach Compliant (Article 33) | No             |
| ROHS Compliant               | Yes            |
| UL Listed (US and Canada)    | Yes            |
| UL Listed (US)               | Yes            |
| Package Quantity (Imperial)  | 1              |
| Package Quantity (Metric)    | 1              |
| Customs Number               | 3925900000     |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TSRPI-RB](#)