

Specification Sheet

Part Number: 321-50015



Tubing is 3.5:1, thick wall adhesive lined.

Toughness and weatherability is ideal for low and medium voltage power applications.

Available in 3.28' (1.0 m) lengths, multiple diameters and 1 color (black).

Conveniently packed in a display carton.

Heat Shrink Tubing, 4' Long Stick, Thick Wall Adhesive Lined, Up to 3.5:1, 2.75", 68/22 dia, PO, Black, 1/pkg

Article Number

321-50015

Type

TREDUX HA47-48ST-68/22

Color

Black (BK)

Quantity Per

pcs.

Product Description

TREDUX HA47 thick wall heat shrink tubing has a adhesive liner that provides good moisture sealing and weather protection suitable for insulation and protection of low and medium voltage power applications. HA47 is tough and the weatherability makes it suitable for exposed applications and underground cable joints. Polyolefin material is pre-cut into 3.28' (1.0m) sticks and stored in a convenient display box. RoHS approved and Halogen free.

Short Description

Heat Shrink Tubing, 4' Long Stick, Thick Wall Adhesive Lined, Up to 3.5:1, 2.75", 68/22 dia, PO, Black, 1/pkg

Global Part Name	TREDUX HA47-48ST-68/22-PO-X-BK
Length L (Imperial)	4.0
Length L (Metric)	1.0
Voltage Range	Low and Medium Voltage
Variant	Thick-Wall
Nominal Diameter (Imperial)	2.75
Nominal Diameter (Metric)	68
Wall Thickness WT (Imperial)	.161
Wall Thickness WT (Metric)	4.1
Material	Polyolefin, chemically cross-linked (PO-X)
Material Shortcut	PO-X
Adhesive	Hot melt adhesive
Flammability	Not flame retardant
Halogen Free	Yes

Operating Temperature -67°F to +230°F (-55°C to +110°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 3926909988

Weight (Imperial) 2.54

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[321-50015](#)