

Specification Sheet

Part Number: 558-00327



Continuous Colored Signal Panel labels come with yellow or orange stripes for easy printing of caution and warning labels. Continuous labels allow for designing and cutting labels to any length. Various widths are available so that a wide variety of sign sizes can be customized and produced on demand.

Adhesive Labels, Banded Color Continuous Roll, 2.0" x 250', PET, Orange/White, 250 ft/roll

Article Number	558-00327
Type	HT2OE50250
Color	Orange (OG)
Quantity Per	roll

Product Description

The Pre-Printed Colored Header Vinyl Rolls can be used to design signs that conform to Occupational Safety and Hazard Association (OSHA) and American National Standards Institute (ANSI) requirements for Warning and Caution Signs and markers. All can be designed, printed and cut to length in Tagprint Pro and any HellermannTyton thermal transfer printing system.

Short Description

Adhesive Labels, Banded Color Continuous Roll, 2.0" x 250', PET, Orange/White, 250 ft/roll

Global Part Name	HT2OE50250-336/926-OG
Technical Description	Banded Colored Continuous Roll, 2.0" X 250', Orange/White
Length L (Imperial)	250.0
Length L (Metric)	76.2
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	2.0
Width W (Metric)	50.8
Thickness T (Metric)	64.0
Width of Liner (Metric)	50.8
Width of Liner (Imperial)	2.0
Material	Type 336/926, Polyester, UV-stabilized, clear polyester laminate (336/926)
Material Shortcut	336/926
Adhesive	Acrylic
Halogen Free	No

Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CSA UL 969
UL Recognized (US)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[558-00327](#)