

Specification Sheet

Part Number: 558-00503

Continuous Polyester Labels are made with UV stable materials for long outdoor life.

Labels use UV stable permanent ink.

Continuous polyester is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.



Adhesive Labels, Solid Color Continuous Roll, 3.0" x 100', UV Stable PET, Red, 100 ft/roll

Article Number 558-00503

Type HT3RDHB250

Color Red (RD)

Quantity Per roll

Product Description Colored continuous rolls offer a high bond adhesive that is sustainable for low surface energy substrates such as the low density plastics on the front of an inverter or powder coat paint surfaces. The adhesive is designed to adhere to textured surfaces without peeling or falling off.

Short Description Adhesive Labels, Solid Color Continuous Roll, 3.0" x 100', UV Stable PET, Red, 100 ft/roll

Global Part Name	HT3RDHB250-840/281-RD
Technical Description	Solid Colored Continuous Roll, Reflective, 3.0" X 100', Red
Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	3.0
Width W (Metric)	76.2
Width of Liner (Metric)	76.2
Width of Liner (Imperial)	3.0
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)

Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2011 IFC 2012 UL 969 NEC2014 CSA 66956 ANSI Standard Z535.4
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[558-00503](#)