

Specification Sheet

Part Number: TAGPHONE



Cardstock paper can be printed using a wide variety of printing methods, including laser, inkjet and dot matrix printers, which means more options for creating and mounting wall outlets and phones.

Inkjet Label, .38" x 1.75", 84 Per Sheet, PAP, White, 1000/pkg

Article Number 593-00001

Type TAGPHONE

Color White (WH)

Quantity Per pack

Product Description HellermannTyton offers a series of technologically advanced labels for use on standard ink jet printers. The labels come on 8.5 x 11" sheets and are printable using HellermannTyton's TagPrint Pro software. A wide range of materials and sizes is available for wire and component marking. Even colors can be printed when used on a color ink jet printer. Ink jet labels are available in polyester or paper.

Short Description Inkjet Label, .38" x 1.75", 84 Per Sheet, PAP, White, 1000/pkg

Global Part Name	TAGPHONE-PAP-WH
Width W (Imperial)	1.75
Width W (Metric)	44.45
Thickness T (Metric)	64.0
Height H (Imperial)	0.375
Height H (Metric)	9.52
Material	Paper (PAP)
Material Shortcut	PAP
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919905060
Labels per Column	21
Labels per Row	4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TAGPHONE](#)