

Specification Sheet

Part Number: GWT003X2



Mounting hole for easy attachment using standard cable ties.

Ground Wire Tag, Telephone Warning, Polyethylene, Orange, 25/pkg

Article Number 597-00037

Type GW

Color Orange (OG)

Quantity Per pack

Product Description HellermannTyton ground wire tags are fabricated using .035" thick polyethylene. Vinyl is rated for outdoor use, 5-7 years. Vinyl treated with titanium dioxide ultraviolet inhibitors.

Short Description Ground Wire Tag, Telephone Warning, Polyethylene, Orange, 25/pkg

Global Part Name GW-PE-OG

Technical Description	Ground Wire Tag, Telephone Warning, Orange
Width W (Imperial)	3.0
Width W (Metric)	76.2
Height H (Imperial)	1.5
Height H (Metric)	38.1
Material	Polyethylene (PE)
Material Shortcut	PE
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature	-150°F to +149°F (-101°C to +65°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[GWT003X2](#)