

Specification Sheet

Part Number: FOM-75

Manufactured from thick .05" polyethylene for long term durability.
Mounting holes for easy mounting using standard cable ties.

Markers can be mounted in any direction, either vertically, horizontally, as a wrap-around identification plate or as a flag for the best visual position on the cable assembly.



Fiber Optic Cable Marker, 1.5" x .75", Polyethylene, Orange, 25/pkg

Article Number	597-00039
Type	FOM
Color	Orange (OG)
Quantity Per	pack
Product Description	HellermannTyton's cable markers are made from .05" thick polyethylene and can be marked using a permanent felt tip marker.
Short Description	Fiber Optic Cable Marker, 1.5" x .75", Polyethylene, Orange, 25/pkg
Global Part Name	FOM-PE-OG

Length L (Imperial)	1.5
Length L (Metric)	19.05
Width W (Imperial)	1.5
Width W (Metric)	38.1
Height H (Imperial)	0.75
Height H (Metric)	19.05
Material	Polyethylene (PE)
Material Shortcut	PE
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature	-150°F to +149°F (-101°C to +65°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes

Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988
Weight (Metric)	0.453
Weight (Imperial)	.2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FOM-75](#)