

Specification Sheet

Part Number: GT.75X1803



Features quick release for repetitive access to cable and wire.
Can be opened and closed numerous times without failure.
Adjustable so one size can accommodate multiple bundle sizes.

Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Orange, 1/pkg

Article Number 854-44389

Type GT.75X180

Color Orange (OG)

Quantity Per bag

Product Description For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

Short Description Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Orange, 1/pkg

Global Part Name GT.75X180

Length L (Imperial) 15.0

Length L (Metric) 4.5

Width W (Imperial) 0.75

Width W (Metric) 19.05

Material Polyethylene (PE) Polyamide (PA)

Material Shortcut PE PA

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 1

Package Quantity (Metric) 1

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[GT.75X1803](#)