

Specification Sheet

Part Number: PFCLC10G

Factory-polished zirconia ceramic ferrules for quick and reliable field installations

Unique wedge clip retains connector shape for precision connection

Easy to use- no epoxy, heat curing, polishing or special tools required

Color coded for easy identification

Meet ANSI/TIA/EIA 568-B standards

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements



Connector, Fiber Optic LC Multimode OM3 (50/125), Pre-Polished (Cleave & Insert), 1/Pkg

Article Number 855-14209

Type PFCLC

Color Aqua (AE)

Quantity Per bag

Product Description Pre-polished connectors provide high performance and eliminate the need for the time consuming task of hand polishing ferrules in the field. A factory pre-cleaved fiber stub and index-matching gel combine to offer an immediate low loss termination of single mode or multimode fiber.

| | |
|------------------------------------|---|
| Short Description | Connector, Fiber Optic LC Multimode OM3 (50/125), Pre-Polished (Cleave & Insert), 1/Pkg |
| Global Part Name | PFCLC |
| Technical Description | Pre-Polished LC 10G 50/125 Multimode Fiber Connector, Aqua |
| Port Count | 2 |
| Package Quantity (Imperial) | 1 |
| Package Quantity (Metric) | 1 |
| Customs Number | 8536700000 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[PFCLC10G](#)