

Specification Sheet

Part Number: PFCST10G

- Factory-polished zirconia ceramic ferrules for quick and reliable field installations
- Unique wedge clip retains connector shape for precision connection
- Easy to use—no epoxy, heat curing, polishing or special tools required
- Color coded for easy identification
- Meet ANSI/TIA/EIA 568-C standards
- Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements



Connector, Fiber Optic ST Multimode OM3 (50/125), Pre-Polished (Cleave & Insert), 1/pkg

Article Number 855-14213

Type PFCST

Color Aqua (AE)

Quantity Per bag

Product Description Pre-polished connectors provide high performance and eliminate the need for the time consuming task of hand polishing ferrules in the field. A factory pre-cleaved fiber stub and index-matching gel combine to offer an immediate low loss termination of single mode or multimode fiber.

Short Description	Connector, Fiber Optic ST Multimode OM3 (50/125), Pre-Polished (Cleave & Insert), 1/pkg
Global Part Name	PFCST
Technical Description	Pre-polished ST 10G 50/125 Multimode Fiber Connector, Aqua
Port Count	1
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8536700000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[PFCST10G](#)