

Specification Sheet

Part Number: CL-T40-10



Rapid installation requiring no specialized tools saves time and money. Highly repeatable – the quality of the seal is not dependent on the skill of the engineer.

Tested beyond a 20-foot water head (58.8kPa), exhibiting excellent sealing properties.

Cablelok T40 24.5 - 29.0 mm x 10, CR, Black, 1/pkg

Article Number	857-50186
Type	CABLELOK-T40-10
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton's patented Cablelok mechanical seal enables fast, safe cable installation, providing a repeatable and consistent seal between the cable and the closure port with excellent non-leak performance. Installation times are typically reduced by up to 90 percent.
Short Description	Cablelok T40 24.5 - 29.0 mm x 10, CR, Black, 1/pkg
Global Part Name	CABLELOK-T40-10

Technical Description	The T Port Cablelok is a mechanical seal manufactured from external grade flexible polychloroprene. There are 5 Cablelok's which cover a cable range of 15.5mm – 29.0mm including a port plug for blocking unused T sized drop ports.
Contents of pkg/kit	10 x CABLELOK-T40(T3), 20 x Lubricating Wipes
Port Count	1
Variant	Round - T
Material	Chloroprene Rubber (CR)
Material Shortcut	CR
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	9030400000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CL-T40-10](#)