

Specification Sheet

Part Number: LCSMINSERT-I

All single mode, single mode angled and multimode 10 Gb inserts feature durable zirconia ceramic ferrules, which allow for frequent, repeated insertion.

All standard multimode inserts feature phosphor bronze ferrules, which provide an affordable insert option.

Color coded for easy fiber selection.

Meet ANSI/TIA/EIA 568-C standards.

Product Image

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.

LC Singlemode Fiber Module, Blue, Ivory, 1/pkg

| | |
|-----------------------|----------------------|
| Article Number | 904-00744 |
| Type | LCSMINSERT-I |
| Color | Ivory (IV) Blue (BU) |
| Quantity Per | box |

Product Description Fiber inserts provide the final connection when using fiber as a digital loop carrier, or fiber-to-the-x solution. HellermannTyton offers a variety of fiber inserts with industry standard LC, SC, ST and MTRJ connections that can be used with HellermannTyton standard flush wall plates.

Short Description LC Singlemode Fiber Module, Blue, Ivory, 1/pkg

Global Part Name LCSMINSERT-I-PL-BGE/BU

Technical Description

LC Single mode Fiber Module, Blue, Ivory

Material

Plastic (PL)

Material Shortcut

PL

Package Quantity (Imperial)

1

Package Quantity (Metric)

1

Customs Number

8536700000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[LCSMINSERT-I](#)