

Technical data sheet

Article number:
150-55940

T30RFT5



Product Group	2-piece fixing ties with fir tree, with disc, for round holes
Product Family	Fir tree parts FT5
Material	Polyamide 6.6, heat stabilised (PA66HS)
Colour	Black (BK), Grey (GY)
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
Bundle Diameter max (metric)	34.0 mm
Bundle Ø min.	5.0 mm
Cable Tie	Polyamide 6.6, heat stabilised (PA66HS)
Fixation Method	Fir Tree
Flammability	UL 94 V2
Foot Part	Polyamide 6.6 (PA66)
for Hole Ø (FH)	4.5 - 5.0 mm
Height (H)	1.2 mm
Length (L)	150 mm
Length (L2)	11.6 mm
Min.Tensile Strength	135 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	500 pcs.
Panel Thickness	3.0 mm
Panel Thickness min. (metric)	0.7 mm
ROHS compliant	Yes
Thickness (T)	1.1 mm
Variant	Inside Serrated
Width (W)	3.5 mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[150-55940](#)