

## Technical data sheet

Article number:  
156-01642

**T50RFT9X17A2SET**

|                                      |                                                                           |
|--------------------------------------|---------------------------------------------------------------------------|
| <b>Material</b>                      | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV) |
| <b>Colour</b>                        | Black (BK)                                                                |
| <b>Bundle Diameter max (metric)</b>  | 50.0 mm                                                                   |
| <b>Bundle Ø min.</b>                 | 5.0 mm                                                                    |
| <b>Cable Tie</b>                     | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV) |
| <b>CE Certification</b>              | No                                                                        |
| <b>Fixation Method</b>               | Fir Tree for oval holes                                                   |
| <b>for Hole Ø (FH)</b>               | 9.0 x 17.0 mm                                                             |
| <b>Length (L)</b>                    | 25.5 mm                                                                   |
| <b>Min.Tensile Strength</b>          | 225 N                                                                     |
| <b>Operating Temperature</b>         | -40 °C to +105 °C                                                         |
| <b>Package Content packed in</b>     | box                                                                       |
| <b>Pack Cont.</b>                    | 2000 pc.                                                                  |
| <b>Panel Thickness</b>               | 5.5 mm                                                                    |
| <b>Panel Thickness max.</b>          | 0.6 - 5.5 mm                                                              |
| <b>Panel Thickness min. (metric)</b> | 0.6 mm                                                                    |
| <b>ROHS compliant</b>                | Yes                                                                       |
| <b>Variant</b>                       | Inside Serrated                                                           |
| <b>Width (W)</b>                     | 20.3 mm                                                                   |

**RoHS** 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-01642](#)