

Technical data sheet

Article number:
156-02747

T50R0SBS5-6UBSET

Material	Polyphenylene Sulfide (PPS)
Colour	Silver (SR)
Bundle Diameter max (metric)	44.5 mm
Bundle Ø min.	2.0 mm
Cable Tie	Polyphenylene Sulfide (PPS)
CE Certification	No
Fixation Method	Weld Stud Fixing
for Hole Ø (FH)	M5 x 0.8, M6 x 1, T5
Height (H)	18.75 mm
Length (L)	202.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +150 °C
Package Content packed in	bag
Pack Cont.	3000 pcs.
ROHS compliant	Yes
Stud Ø	5.0 mm, 6.0 mm
Width (W)	8.14 mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02747](#)