

Technical data sheet

Article number:
157-00038

T50SOSSBD-M6

Product Group	1-piece fixing ties for weld studs
Product Family	T50SOSSBD for cable routing alongside and below the stud
Material	Polyamide 6.6, heat and UV-stabilised (PA66HSUV)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, EVOcut, MK9P, MK9P w/ Upper air, MK10-SB, MK21, EVO9SP, EVO9HT, EVO9i, EVO9iSP, EVO9iHT
Bundle Diameter max (metric)	30.0 mm
Bundle Ø min.	3.0 mm
Fixation Method	Weld Stud Fixing
Flammability	UL 94 V2
Length (L)	175.0 mm
Min.Tensile Strength	150 N
Mounting Screw Type	M6 Screw
Operating Temperature	-40 °C to +110 °C
Package Content packed in	bag
Pack Cont.	100 pcs.
ROHS compliant	Yes
Stud Ø	M6
Thickness (T)	1.3 mm
Variant	Outside Serrated
Width (W)	5.7 mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00038](#)