

Technical data sheet

Article number:
157-04015

T80ROSLPSB5-6U

Product Group	1-piece fixing ties for weld studs
Material	Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS)
Colour	Orange (OG), High Voltage (HV)
Bundle Diameter max (metric)	50.0 mm
Bundle Ø min.	3.5 mm
CE Certification	No
Fixation Method	Stud Mount
Flammability	UL 94 HB
for Hole Ø (FH)	M6 x 1, M5 x 0.8, T5, T6
Height (H)	6.30 mm
Length (L)	208.3 mm
Min.Tensile Strength	355 N
Operating Temperature	-40 °C to +110 °C
Package Content packed in	carton
Pack Cont.	2500 pcs.
ROHS compliant	Yes
Stud Ø	5.0 mm, 6.0 mm
Thickness (T)	1.4 mm
Width (W)	14.22 mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-04015](#)