

R8A77800BNBG

User's Manual: Hardware



- [Product Info](#)
- [Design Support](#)
- [Documentation](#)
- [Sample Code](#)
- [Software & Tools](#)
- [Ordering](#)

Product Spec



- [Basic Information](#)
- [Memory](#)
- [CPU \(Bit, Clock, DMA, External Bus etc\)](#)
- [Timers](#)
- [Interfaces](#)
- [Operating Conditions](#)
- [Package](#)

Basic Information

Product Status	Mass Production
Family	SuperH
Series	SH7780
Group	SH7780

Memory

Program memory	0 KB ROMless
RAM	16 KB
Cache Memory Remark	32 KB (instruction), 32 KB (operand), 4-way set associative

CPU (Bit, Clock, DMA, External Bus etc)

CPU	SH-4A (32-bit)
------------	----------------

Recommended Product

Orderable Part Name **R8A77800BNBGV#UM**

Star Product -

Product Longevity Program (PLP)

Production Status **Mass Production**

EU RoHS -

RoHS-pdf (China-RoHS) -



Max. Frequency	400 MHz
PLL	YES
Real-Time Clock (RTC)	YES
Power-On Reset	YES
Memory Management Unit	YES
Floating Point Unit	YES
DMA Remarks	DMAC x 12 ch
External Address/Data Bus	YES
External Interrupt Pins	9
I/O Ports	83



 [Back to Top](#)

Timers	
16-bit Timers	4 ch
32-bit Timers	6 ch
Watchdog Timers	1 ch

Interfaces	
CSIs	4 ch
SPIs	1 ch
UARTs	2 ch
Serial Interface Remarks	SCIF (CSI:2ch/UART:2ch), SIOF (CSI:1ch), HSPI (SPI:1ch), SSI (CSI:1ch)

Operating Conditions	
Operating Voltage	3 to 3.6 V
Power Supply	VDDQ = 3.0 to 3.6V, VDD = 1.25V
Operating Temperature	-20 to 75 °C (Ambient Temperature)



Package	
Pins	449
Terminal pitch (mm)	0.8 mm
Package Type	FBGA
Dimensions (mm)	21x21 mm ²
Drawing Link	 prbg0449ga_a
Mount pad	 fig0013e
Mounting height (mm)[MAX]	1.9 mm
Mass (g) [TYP,]	1.4 g
Renesas code	PRBG0449GA-A (old: BP-449V)
JEITA code	P-FBGA449-21x21-0.80
Terminal material - Base	Sn-Ag-Cu
Terminal material - Surface	-

 [Back to Top](#)



Need More Help ?

[Contact Us](#) [Website Feedback](#)

[Distributors](#) [Videos](#)

[Forums](#) [Knowledgebase](#)

Others

[Mobile App](#) [Privacy Policy](#)


[Legal](#)

[Sitemap](#)

Follow Us

 [Facebook](#)

 [Twitter](#)

 [YouTube](#)

© 2010-2017 Renesas Electronics Corporation. All rights reserved.



Sign in Americas

- Solutions
- Products
- Design & Support
- About
- Special Offers
- Parametric search
- History

Home > Microcontrollers and Microprocessors > SuperH RISC engine Family > SH7780

Share Add to my favorites

R8A77800BNBG

User's Manual: Hardware



- Product Info
- Design Support
- Documentation
- Sample Code
- Software & Tools
- Ordering

Orderable Part Name	Package Code	Production Status	Request Samples	Request Pricing	Distributor Stock	Distributors	Distributor Purchase	EU RoHS	RoHS-pdf (China-RoHS)	1000 Piece Budgetary Price	Star Product	Product Longevity Program (PLP)
R8A77800BNBGV#UM	[object Object]	-	Mar, 2025	Mass Production	-	-	call	-	-	-	-	Contact
R8A77800BNBGV	[object Object]	-	Mar, 2025	Mass Production	-	-	call	-	-	2	ARROW ELECTRONICS INC.	Buy

Note :Distributor Prices may vary from the stated budgetary price. The pricing and availability information on this site is based on information provided by Renesas' authorized distributors and is subject to change without notice. By selecting a distributor from this page, you will be redirected from the Renesas site to the distributor's website to complete a purchase. The distributors are independent from Renesas and maintain their own terms and conditions of sale. Renesas disclaims all representations and warranties, express and implied, with respect to transactions between distributors and their end customers.

Related Tool

Tools Orderable Part Number(s)	Production Status	Manufacturer	Suggested Single Tool Price	Description	Distributor Stock	Distributors	Distributor Purchase
YRTA-HEWSH-1UL	Mass Production	Renesas	\$2557.54	HEW IDE & C Compiler SH 1 User LAN	-	-	Contact
YRTA-HEWSH-1U	Mass Production	Renesas	\$2382.35	HEW IDE & C Compiler SH 1 User + HW Key	-	-	Contact
HS0005KCU02H	Mass Production	Renesas	\$1905.88	On-Chip Debug Emulator E10A-USB w/ Trace	-	-	Contact
HS0005KCU01H	Mass Production	Renesas	\$1152.94	On-Chip Debug Emulator E10A-USB	4	ARROW ELECTRONICS INC.	Buy

Recommended Product

Orderable Part Name	R8A77800BNBGV#UM
Star Product	-
Product Longevity Program (PLP)	
Production Status	Mass Production
EU RoHS	-
RoHS-pdf (China-RoHS)	-



Note :Distributor Prices may vary from the stated budgetary price. The pricing and availability information on this site is based on information provided by Renesas' authorized distributors and is subject to change without notice. By selecting a distributor from this page, you will be redirected from the Renesas site to the distributor's website to complete a purchase. The distributors are independent from Renesas and maintain their own terms and conditions of sale. Renesas disclaims all representations and warranties, express and implied, with respect to transactions between distributors and their end customers.

 [Back to Top](#)

Need More Help ?

[Contact Us](#) [Website Feedback](#)

[Distributors](#) [Videos](#)

[Forums](#) [Knowledgebase](#)

Others

[Mobile App](#) [Privacy Policy](#)


[Legal](#)

[Sitemap](#)

Follow Us

 [Facebook](#)

 [Twitter](#)

 [YouTube](#)

© 2010-2017 Renesas Electronics Corporation. All rights reserved.



Live
Chat
Offline

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Renesas Electronics:](#)

[R8A77800BNBGV](#)