



THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	CLASS A RELEASED	10/19/2023	B. Hansen

NOTES:

- ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.
- MATERIAL:
 - MDP CONNECTOR -
 - MOLDED BODY: POLYPROPYLENE (PP), BLACK.
 - 4mm BANANA PLUGS -
 - BODY: BRASS, NICKEL PLATED.
 - CAGE CONTACT: BECU, NICKEL PLATED.
 - RG58C/U COAX CABLE -
 - JACKET: PVC, BLACK; ϕ 4.95 O.D.
 - DIELECTRIC: PE
 - CENTER CONDUCTOR: 22 AWG (19X34) TINNED COPPER, STRANDED.
 - BREAKOUT: PVC, BLACK
 - 4mm STACKING RETRACTABLE SLEEVE BANANA PLUGS -
 - BODY: BRASS, NICKEL PLATED.
 - INSULATOR (BODY): PP, COLOR SAME AS WIRE. TIP, PP, GREY.
 - CONTACT: BECU, NICKEL PLATED
- ELECTRICAL:
 - IMPEDANCE:
 - ASSEMBLY: NON-CONSTANT
 - RG58C/U: 50 Ω
 - VOLTAGE -
 - 30 VRMS / 60 VDC (HANDHELD)
 - 500 VRMS (HANDS FREE)
 - DO NOT USE ON CIRCUITS SUBJECT TO TRANSIENT OVERVOLTAGES.
 - CURRENT: 3 A MAX.
- MECHANICAL:
 - OPERATING TEMPERATURE: 0°C TO +50°C
 - CABLE BEND RADIUS:
 - REPEATED MIN. - 49.8 mm
 - ONE-TIME MIN. - 25 mm
- CE MARK:
 - ROHS 2 COMPLIANT.
 - UKCA COMPLIANT.



CT4455-100	100 ± 1.5	-100
MODEL NUMBER	LENGTH & TOLERANCE (cm)	MODEL NUMBER -XXX EXTENSION

MODEL NUMBER TABLE			
THIRD ANGLE PROJECTION	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: X.X = ±0.5 X.X* = ±0.5* X.XX = ±0.25 X.XXX = ±0.125 DO NOT SCALE DRAWING	PROJECT NO. A660(b)	METRIC  22820 Savi Ranch Prky. Yorba Linda, CA 92887 USA
	MATERIAL SEE NOTES	APPROVALS DRAWN WDH CHECKER	TITLE CABLE ASSEMBLY, MDP TO 4mm STK RETRACTABLE SLEEVE BANANA PLUG BREAKOUTS, RG58C/U
REFERENCE	TREATMENT NONE	ENGR. B. HANSEN DESIGN ACTIVITY	DATE 10/18/2023 6/3/2021
	FINISH SEE NOTES	SIZE B SCALE 1:1	CAGE CODE 43F45 DWG. NO. CT4455 REV. A
			SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4455-100](#)