


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	CLASS A RELEASED	5/1/2023	B. HANSEN
B	ADDED ISOMETRIC VIEW.	6/5/2023	B. Hansen

NOTES:

- INSULATED ALLIGATOR CLIP LEAD ASSEMBLY.
- SPECIFICATIONS:
 - ALLIGATOR CLIPS:
 - CONDUCTOR: STEEL, NICKEL PLATED.
 - TIP INSULATORS: POLYPROPYLENE 3084H, FILE# E216959. (COLOR MATCHES WIRE).
 - SPRING: STAINLESS STEEL
 - BOOT: TPR (SANTOPRENE 201-55, FILE# E80017). COLOR MATCHES WIRE.
 - TEST LEAD: SILICONE JACKETED, DOUBLE-INSULATED, BARE COPPER, STRANDING 195x0.07mm, 0.75mm², 18AWG. (EASSAN, 3239 AWM, VW-1, UL 758, cULus). COLOR - SEE MODEL NUMBER.
- RATING:
 - IEC VOLTAGE: 1000 V CAT III / 600 V CAT IV.
 - CURRENT: 10 A MAX.
 - TEMPERATURE: 0°C TO +60°C MAX
- RoHS 2 COMPLIANT.
- AVAILABLE AS MODEL CT4485-L, BLACK AND RED PAIR OF CT4484-L-#.



MODEL NUMBER

CT4484-L- #

COLOR: **0** - BLACK
2 - RED

LENGTH: (cm)



ISOMETRIC VIEW
SCALE 1:2
(RED SHOWN)

THIRD ANGLE PROJECTION 	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: X.X = ±0.5 X.X* = ±0.5* X.XX = ±0.25 X.XXX = ±0.125 DO NOT SCALE DRAWING	PROJECT NO. A645(a)	METRIC	Cal Test ELECTRONICS	22820 Savi Ranch Prky. Yorba Linda, CA 92887 USA
		APPROVALS	DATE	TITLE LEAD, ALLIGATOR CLIPS, 1000V CAT III, SILICONE 18AWG	
REFERENCE	TREATMENT NONE	ENGR. B. HANSEN	5/1/2023	SIZE B	CAGE CODE 43F45
	FINISH SEE NOTES	DESIGN ACTIVITY		DWG. NO. CT4484	REV. B
SCALE 1:1				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4484-100-0](#) [CT4484-100-2](#) [CT4485-100](#)