



Datasheet revision 1.0

www.Proto-Advantage.com

SOIC-16 with 0805, 1206 SMT Adapter Breadboard

Product Highlights

Immersion Gold Finish
Single Sided
RoHS 3 and REACH Compliant

Specifications

Dimensions:	1.6" x 0.95" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C

Description

Surface Mount Solder Bread board. Fits SOIC-16 (150/200 mil) components with extra space for medium density 0805 and 1206 components surrounding.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[SBB0003-1](#)