



Datasheet revision 1.0

www.Proto-Advantage.com

Solder-in breadboard 1500 plated holes

Product Highlights

Immersion Gold Finish
Plated through holes
1500 holes in total
0.1" hole grid
30 rows, 50 columns

Specifications

Dimensions:	5.1" x 3.2" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Hole size:	1.0mm (40 mils) diameter
	Holes accept 25 mil square wire wrap posts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chip Quik:](#)

[SBBTH3050-1](#)