

Customer Part:

Description

- LVPECL output crystal oscillator using a high frequency fundamental crystal to give very low jitter. Hermetically sealed ceramic package with a seam sealed metal lid.
- Model IQXO-623
- Model Issue number 2
- Note: Operating temperature ranges -40 to 105°C and -40 to 125°C are intended for industrial use and not for safety critical applications such as automotive. Please contact IQD for alternative options.

Frequency Parameters

- Frequency 156.250MHz
- Frequency Stability ±50.00ppm
- Operating Temperature Range -40.00 to 105.00°C
- Ageing ±3ppm max per year @ 25°C

Electrical Parameters

- Supply Voltage 2.5V ±5%
- Current Draw 50.000mA

Output Details

- Output Compatibility LVPECL
- Drive Capability 50Ω terminated to Vs-2.0V
- Rise and Fall Time 0.5ns max
- Duty Cycle 45/55%
- Output Voltage Levels:
Output Low (VOL): 1.095V max
Output High (VOH): 1.475V min

Output Control

- Standby Operation:
Logic '1' (70% Vs min) to pad 1 enables oscillator output.
Logic '0' (30% Vs max) to pad 1 disables oscillator output.
No connection to pad 1 enables oscillator output due to internal pull-up resistor.
- Standby Current: 10µA max
- Start-up Time: 10ms max

Noise Parameters



- Phase Jitter (12kHz to 20MHz): 1ps rms max
Phase Jitter (12kHz to 20MHz): 0.171ps rms typ @ 100MHz

Environmental Parameters


- Storage Temperature Range: -55 to 125°C
- Shock: 1500G, 0.5ms, 3 times for each surface, total 18 times.
- Vibration: Freq. range: 20~2000Hz, peak to peak amplitude: 1.52mm, peak acceleration: 20G (196m/s²), 3 direction(X, Y,Z), each cycle: 20min, 4 cycles for each direction.

Manufacturing Details

- RoHS Terminations Au over Ni
- RoHS Reflow Temp 260°C max for 10sec max


Outline (mm)


- Pad Connections
1. Standby Operation
 2. N/C
 3. GND
 4. Output +
 5. Output -
 6. +Vs

Solder Pad Layout

Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

Customer Part:**Compliance**

- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Pack Style: Cutt In tape, cut from a reel
Pack Size: 100
- *Alternative packing option available*

Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFSPXO083327Cutt](#)