






CITEL

UL TYPE 1 SPD - I_{max} 40kA - I_n 20kA - Modular

DS43S-480



- UL1449 TYPE 1 LISTED SPD
- MOV Technology
- 40kA Surge Current Rating
- Visual fault indicator and remote contacts
- 10-Year warranty



Electrical Characteristics

Network		800 V 3-phase
Total Maximum discharge current <i>max. total withstand @ 8/20 μs</i>	I _{max} Total	120 kA
Protection mode(s)		Common mode
POWER SPD TYPE		UL1449 TYPE 1 LISTED
VOLTS	(V)	480
AC/DC/DC PV/RF		AC
PHASE	(PH)	3D
AMPS	(A)	N/A
AMBIENT MIN	(C)	-35
AMBIENT MAX	(C)	+60
MODES		L-L, L-G
VPR	(V)	4000/-/1800/-
MCOV	(V)	550/-/550/-
IN 15 impulses 8/20μs	(kA)	20
SCCR	(kA)	100
IMAX 8/20μs	(kA)	40
Iimp 10/350μs	(kA)	4

Option

RFI Filter		no
------------	--	----

Installation

Wiring type		Screw
Solid wire cross section <i>Min</i>	mm ²	2.5000
Solid Wire cross section <i>Max</i>	mm ²	35.0000
Stranded Wire cross section <i>Min</i>	mm ²	2.5000
Stranded wire cross section <i>Max</i>	mm ²	25.0000
Wire gauge <i>Min</i>	AWG	13.0000
Wire gauge <i>Max</i>	AWG	2.0000
Torque	Nm	2.0 - 2.5
Torque	in-lbs	17.8 - 22.1
Strip Length	mm	13.0000
Strip Length	in	0.5000
Operating Temperature <i>Min</i>	°C	-40.0000
Operating Temperature <i>Max</i>	°C	85.0000
Operating Temperature <i>Min</i>	°F	-40.0000
Operating Temperature <i>Max</i>	°F	85.0000
Operating Relative Humidity <i>Max</i>	%RH	95
Operating Altitude <i>Min</i>	Ft	2000.0000
Operating Altitude <i>Max</i>	Ft	6500.0000
Housing/Enclosure material		Thermoplastic
Flammability rating <i>UL 94</i>		V0
Mounting		Din Rail
IP Environmental rating/ <i>IP</i>		IP20
NEMA Environmental rating/ <i>NEMA</i>		NEMA 1
Installation Location		Indoor
Spare part		Module
Product Dimension <i>L</i>	mm	99.0000
Product Dimension <i>H</i>	mm	67.0000
Product Dimension <i>W</i>	mm	54.0000
Product Dimension <i>L</i>	In	3.8900
Product Dimension <i>H</i>	In	2.6400
Product Dimension <i>W</i>	In	2.1300

Miscellaneous

DS43S-480

Individual Pack		Yes
Storage Temperature _{Min}	°C	-40.0000
Storage Temperature _{Max}	°C	85.0000
Storage Temperature _{Min}	°F	-40.0000
Storage Temperature _{Max}	°F	85.0000
Storage Relative Humidity _{Max}	%RH	95.0000
Mechanical Characteristics		
Technology		MOV
Connection to Network		By screw terminals: 2.5-25mm ² / by bus
Format		Plug-in modular box
Failsafe mode		Disconnection from AC network
Weight		0.31 kg
TECHNOLOGY		MOV
NETWORK CONFIGURATION		3PH, 3W+G, Delta
CONNECTION METHOD		SPD-Screw Terminal (8-12AWG), Terminal blocks 6AWG
MOUNTING		Din Rail
MATERIAL		Thermoplastic UL94-V0
NEMA RATING (IP RATING)		NEMA 2 (IP20)
FAIL-SAFE BEHAVIOR		Disconnection via fuse-link
REAL-TIME DIAGNOSTICS		Visual indicator and remote contacts
DIMENSIONS		See diagram
WEIGHT		0.90 lbs
SPARE PART		DSM40-480
Standards		
Certification		CSA / UL Listed
UL STANDARD		UL1449 5th Edition
UL CATEGORY		VZCA, VZCA7
UL FILE NUMBER		E326289
STANDARDS		NOM-003-SCFI-2014, NOM-001-SCFI-1993
ENVIRONMENTAL STANDARDS		ROHS
Part number		
461017		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Citel:](#)

[DS43S-480](#)