

Directive 2002/95/EC
"RoHS"
Compliant


NOTES:

1. PLATING MATING SIDE.

INNER CONDUCTOR: min. 50µin HARD GOLD over min. 50µin NICKEL

OUTER CONDUCTOR: min. 30µin HARD GOLD over min. 50µin NICKEL

2. FOR CABLE S2



APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
drawn	20.04.2009 Sonnenberg
appd.	20.04.2009 Fischer
norm	
d-old	

scale:	5:1	
material:		
title:	COAXIAL CONTACT MALE 50 OHM	
	Inner conductor for solder termination	
	outer conductor for crimp or solder termination	
dwg no:	Inventor 10	DIN-A3
	13K2A030A	sh: 1
part no:	131J20059X	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131J20059X](#)