



Directive 2002/95/EC
"RoHS"
Compliant

No. of pos.	A ±0.2	B ±0.1	C ±0.2	D ±0.1	E	Part-NO.
10	32.00	27.94	17.82	4x2.54=10.16	50.00	141A10379X
14	37.08	33.02	22.90	6x2.54=15.24	55.00	141A10389X
16	39.62	35.56	25.44	7x2.54=17.78	57.60	141A10399X
20	44.70	40.64	30.52	9x2.54=22.86	62.50	141A10409X
26	52.32	48.26	38.14	12x2.54=30.48	70.10	141A10419X
34	62.48	58.42	48.30	16x2.54=40.64	80.30	141A10429X
40	70.10	66.04	55.92	19x2.54=48.26	87.90	141A10439X
50	82.80	78.74	68.62	24x2.54=60.96	100.70	141A10449X
60	95.50	91.44	81.32	29x2.54=73.66	113.40	141A10459X
64	100.58	96.52	86.40	31x2.54=78.74	118.52	141A12339X

NOTES:

- INSULATORS: PBT GV, V0 UL 94, GREY
- CONTACTS: PHOSPHOR BRONCE
- OPERATING TEMPERATURE RANGE: -40°C TO +105°C
- CURRENT CARRYING CAPACITY: 1A
- TEST VOLTAGE: 1000 Veff.
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY, WITHOUT WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

2 x b	Ä 3115	24.09.2008	lehmen
a	Origin		
rev.	description	date	name

tolerance	
2002	date
drawn	24.07.
name	Parei
appd.	24.07.
name	E. Mickenbecker
norm	DIN 41651
d-old	

scale: 2:1

material: SEE NOTES

title: **HEADER**
10-64pos. STRAIGHT SOLDER PINS
with long latch

dwg no: AutoCAD 2000 DIN-A 3 sh:1/1

14K1A1010

part no: SEE TABLE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[141A10399X](#)