



Notes:

- Electrical Specifications:
 - Meets USB 2.0 Specification
 - Contact Resistance: 30 mOhm max.
 - Insulation Resistance: 1000 MOhm min. @ 100 VDC
 - Current Rating: 1.5 A max. at 25°C
 - Working Voltage: 30 V (RMS) max.
 - DWV: 500 VAC/60s at sea level
 - Operating Temperature: -40°C to +85°C
- Material and Finish:
 - Receptacle Housing and Protective Cover: Polyester, UL94 V-0, Color: Black
 - or ABS, Nickel Plated, UL94 V-0
 - Panel Nut: Brass, Finish: Nickel Plated
 - Panel and Cover Gasket: Silicon, Color: White
 - Tether: Polycarbonate, Color: Black
 - USB Adaptor Insulator: PBT, UL94 V-0, Black
 - USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
 - USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
 - USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel
- Connector can be mounted to a maximum panel thickness of 3.2 mm.
- IP67 rated when covered or fully mated with the appropriated mating connector

Version	Part Number
Black Plastic Version	17-210141
Metallized Plastic Version	17-210181

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER OR ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale:	Dim. in mm		
	Name	Title	Approval Date	0 PLC ±0.50	1 PLC ±0.38		2 PLC ±0.25	3 PLC ±0.10	ANGLES ±3°	
	1 x e	Ä21-0426	03.11.2021	Bub	2012	Date	Name	Material: See Notes		
	d	1 x d	May/05/2014	Vincent Ke	Draw.	Sept. 28	Vincent Ke	Receptacle + Cover Assembly Kit		
	c	3 x c	Jan/18/2013	Vincent Ke	Appd.	Sept. 28	J. Chaudry	Both Sides Bayonet Receptacle Housing with USB Type A F/F Adaptor		
b	1 x b	Oct/17/2012	Vincent ke	Norm			Drawing No.: 17K1A357		DIN A3	
a	original			D-old			Part No.: SEE PART NUMBER TABLE		Sheet 1/1	
Rev	Changes	Date	Name							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-210181](#)