

Technical specification :

Rated voltage: 30 V
IEC 61076-2-101

Current rating: 3 A at 40°C
IEC 61076-2-101

Insulation resistance: >=100 M
IEC 60512

Pollution degree: 3/2
IEC 60664-1

Degree of protection: IP 67, in mated condition
IEC 60529

Temperature range: -30°C ... +80°C
EN 60512-11-10
-40°C ... +85°C
EN 60512-11-4

Mating cycles: >=100
IEC 60512-9a

Materials:

Contact: CuZn, Ni b / Au 0,2 gal.

Contact carrier: PA, UL 94 V-0

Sealing: FPM

Coupling nut/ screw: GD-Zn, Nickel plated

Moulding body: TPU, UL 94 HB, grey

Installation specification:


Recommended torque: 0,4 Nm

Conec installation tool: Torque wrench: 36-000200
Insert across flats 9: 36-000210

Part no:	Description:
42-05104	SAL - 8 - YS4 - 2YK4

DO NOT ALTER CAD DRAWING BY HAND

RoHS & REACH compliant



dim. in mm

	date	name
drawn	23.11.15	Willer
appd.	23.11.15	Franz

general tolerance:	0	± 0,50mm
	0,0	± 0,25mm
	0,00	± 0,10mm
	*	± 5°



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

title:

Y-splitter, male connector M8x1 - 2x female connector M8x1

dwg no:

42K1A1217

part no:

see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[42-05104](#)