

**Technical specification:**

Degree of protection: IP 67, in mated condition  
IEC 60529  
Temperature range: -30°C ... +120°C

**Materials:**

Protecting cap: PA GF

**Installation specification:**


Recommended torque: 0,6 Nm

Part no:	Description:	Colour:
43-16211	Protecting cap M12x1 female socket	black

title:		Protecting cap M12x1, female socket
dwg no:		
		43K1A1797
part no:		see table

DO NOT ALTER CAD DRAWING BY HAND

Directive 2002/95/EC RoHS compliant



dim. in mm

	date	name
drawn	30.10.12	Kniesburgers
appd.	30.10.12	Franz

general tolerance:	0 ± 0,50mm
	0,0 ± 0,25mm
	0,00 ± 0,10mm



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[43-16211](#)