

Technical specification:


Rated voltage: IEC 60664-1	300 V
Current rating: IEC 60512-3	13 A at 40°C
Insulation resistance: IEC 60512	≥100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range:	-25°C ... +80°C
Mating cycles: IEC 60512-9a	≥100

Materials:

Contact:	CuZn
Contact plating:	Nickel, silver plated
Contact carrier:	PA GF, UL 94
Sealing:	FPM
Coupling nut:	PA GF, UL 94
Moulding body:	TPU, UL 94, grey

Contact assignment:

1)	brown	_____
2)	blue	_____
3)	black	_____
PE)	green-yellow	_____



D see data sheet cable

Part no:	Description:	Length L:	Cable:
41-51008	SAL - 24 - RKW3PE - 2 / A3	2m	PVC, UL 2464, grey, 4x1,5mm ² Cable: 781-A38400
41-51009	SAL - 24 - RKW3PE - 3 / A3	3m	
41-51010	SAL - 24 - RKW3PE - 5 / A3	5m	
41-51011	SAL - 24 - RKW3PE - 10 / A3	10m	
41-xxxxx	SAL - 24 - RKW3PE - ... / A3	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2011/65/EU RoHS compliant	Index: c 03.03.2014 rbo - Ä5117 technical specification changed, Temperature was -40°C ... +80°C	dim. in mm		title: Female connector RD24 angled
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%	date	name	
		drawn	19.10.07	Mankopf
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm	appd.	19.10.07	Franz
CONEC ®				part no:

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[41-51009](#) [41-51010](#) [41-51008](#) [41-51011](#)