



**NOTES:**

1. METALHELLS: STAINLESS STEEL;
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY  
PLATING: 50µin HARD GOLD over min. 50µin NICKEL  
SOLDER CUP ACCEPTS CABLE AWG 20
4. CONNECTOR IS PART MARKED: DSSGXSMJD01X CONEC ABC

Directive 2002/95/EC  
„RoHS“  
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			
DO NOT ALTER CAD DRAWING BY HAND			
a	Origin	date	name
rev.	description	date	name

tolerance ISO 2768-m	dim. in mm	scale: 2:1 (5:1)
date	name	material: SEE NOTES
drawn: 03.03.2008	Sonnenberg	<b>D-SUB MALE</b> 9pos. SOLDER CUP
appd.: 03.03.2008	Kühle	
norm		
d-old		
title:		dwg no: <span style="border: 1px solid black; padding: 2px;">Inventor 10</span>
part no: <span style="border: 1px solid black; padding: 2px;">DSSGXSMJD01X</span>		DIN-A3 sh: 1



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[DSSGXSMJD01X](#)