



plating item 1	part no.
GOLD FLASH over NICKEL	131A12019X
30µm HARD GOLD over min. 50µm NICKEL	131C12019X

3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	TIN PLATED
1	1	MATING SIDE	COPPER ALLOY	SEE TABLE
pos	qty	description	material	plating

partlist		tolerance	dim. in mm	scale:	10:1
				material:	SEE PARTLIST
		date	name	title:	
		drawn	23.03.1998	HIGH POWER CONTACT MALE	
		appd.	23.03.1998	SOLDER PIN STRAIGHT / Ø1,95 / 20A	
		norm		D-SUB COMBINATION	
		d-old		dwg no:	
3 x b	Ä 6216	29.06.2016	Unkrüer		DIN-A3
a	Original			13K11D5A	sh: 1
rev.	description	date	name	part no:	SEE TABLE

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131C12019X](#)