


4

3


2

1


used for: D-SUB



Wire size AWG	Crimp height A
24	0,68 - 0,86
22	0,68 - 0,86
20	0,68 - 0,86



## STRIPPING DIMENSIONS



Finish	Part-NO.
8µ" hard-gold-plated in the contact area	163A20679X
30µ" hard-gold-plated in the contact area	163C20679X

## NOTES:

Material: phosphor bronze

Finish: see table

Temperature range: -55°C to +125°C

Rated current: 7.5A

Contact resistance: &lt;= 10mOhm

Crimping: use crimp tool 360X10079X

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

Directive 2002/95/EC  
"RoHS"  
Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name	tolerance	dim. in mm
		2005	date		
		drawn	07.04.		Lehmenkühler
		appd.	07.04.		Mickenbecker
		norm			
		d-old			
<b>CONEC®</b>					

scale:	5:1
material:	SEE NOTES
title:	<b>PLUG CONTACT</b> CRIMP AWG24-20 ( separate contacts )
dwg no:	AutoCAD 2004
part no:	SEE TABLE
DIN-A	4
sh:	1/1

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[163A20679X](#)