

Product Parameters

Item Features



- * Heavy duty design, Soft start
- * High efficiency, up to 100, 000 hours of service life
- * Non-isolated between input and output
- * Design meeting CE/RoHS
- * 100% full load burn-in test
- * Waterproof level IP68,
- * Die-cast aluminum shell, epoxy potting
- * Internal capacitor: NCC & NICHICON (high reliability)
- * Cooling by free air convection.
- * Safety Protection: Over-voltage, Over-current, Short-circuit and over temperature.

Model No.

WG8-36BC12R610

Type	Lithium battery charger
Input voltage	12V/24V DC
Input voltage range	8-36V DC
Efficiency	96% @ 12Vin
Output voltage	12.6V DC
Output current	10A (constant current)
Voltage regulation	< 1%
Load regulation	< 2%
Ripple & Noise	156mVp-p
Working temperature	-30°C to +80°C
Waterproof rating	IP68
Dimension	74*74*32mm
Weight	290g
Cooling way	Free air convection
Input cable type	14AWG @16.5cm Red/Black
Output cable type	16AWG @16.5cm Yellow/Black
Package	White box
Warranty	1 year

Shenzhen Wengao Electronic Co., Ltd reserves the copyright and right of final interpretation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[PRT-18722](#)