



Expulsion fuse-link, medium voltage, 3 A, AC 25 kV, 660 mm, ANSI, K fast



25KB3

General specifications		
Product name		Eaton Bussmann series medium voltage expulsion fuse
Part no.		25KB3
EAN		5027590470285
Product Length/Depth		225 millimetre
Product height		76 millimetre
Product width		106 millimetre
Product weight		17.52 gram
Compliances		Contact Manufacturer
Certifications		ANSI/IEEE Std C37.42
Product Tradename		None
Product Type		Medium voltage expulsion fuse
Product Sub Type		None
Electrical data		
Amperage Rating		3 A
Voltage rating		25 kV
Current characteristic type		Type K - Complies with ANSI C 37-42 requirements for fast acting K Characteristics
Rated frequency - min		50 Hz
Rated frequency - max		60 Hz
Product specifications		
Application		Primary side transformer protection, feeder protection, capacitor bank protection
Standard		ANSI
Type of termination		Fixed buttonhead

### Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Expulsion fuse-link, medium voltage (EC003611)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Expulsion fuse-link, medium voltage (ecl@ss13-27-14-21-28 [AGH830004])		
Rated current	A	3
Rated voltage	kV	25
Voltage type		AC
Rated frequency	Hz	50 - 60
Release characteristic		K
Type of termination		Fixed buttonhead
Standard		ANSI

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[25KB3](#)