



Expulsion fuse-link, medium voltage, 3 A, AC 25 kV, 660 mm, ANSI, K fast



Part no. 25KV 3A REMOVABLE B/H EXPULSION LINK  
25KBR3

General specifications		
Product name		Eaton Bussmann series medium voltage expulsion fuse
Part no.		25KV 3A REMOVABLE B/H EXPULSION LINK
EAN		5027590470520
Product Length/Depth		225 millimetre
Product height		76 millimetre
Product width		106 millimetre
Product weight		23.24 gram
Compliances		ANSI C37.42
Certifications		Contact Manufacturer
Product Tradename		None
Product Type		Medium voltage expulsion fuse
Product Sub Type		None
Electrical data		
Amperage Rating		3 A
Voltage rating		25 kV
Current characteristic type		Type K - Complies with ANSI C 37-42 requirements for fast acting K Characteristics
Rated frequency - min		50 Hz
Rated frequency - max		60 Hz
Product specifications		
Application		Primary side transformer protection, feeder protection, capacitor bank protection
Standard		ANSI
Type of termination		Removable buttonhead

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Expulsion fuse-link, medium voltage (EC003611)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Expulsion fuse-link, medium voltage (ecl@ss13-27-14-21-28 [AGH830004])		
Rated current	A	3
Rated voltage	kV	25
Voltage type		AC
Rated frequency	Hz	50 - 60
Release characteristic		K
Type of termination		Removable buttonhead
Standard		ANSI

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[25KBR3](#)