



Neutral link, low voltage, 32 A, AC 550 V, BS88/F1, gL/gG, BS

32NNL

General specifications		
Product name		Eaton Bussmann series low voltage british standard fuse holder
Part no.		32NNL
EAN		5027590476966
Product Length/Depth		61 millimetre
Product height		12 millimetre
Product width		13 millimetre
Product weight		5.7 gram
Compliances		Contact factory
Product Tradename		None
Product Type		Low voltage british standard fuse holder
Product Sub Type		None
Electrical data		
Amperage Rating		32 A
Class		Class gG/gL

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC solid link (EC000026)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC solid link (ecl@ss13-27-14-21-05 [AKE277018])		
Rated current	A	32
Power loss at rated current	W	
Construction size		Other

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[32NNL](#)