

4x4 HDMI Matrix Switch with Remote Control - 1080p @ 60 Hz (HDMI 4xF/4xF), TAA

MODEL NUMBER: B119-4X4



Connect 4 HDMI source devices to 4 HDMI displays and switch video signals between them.

Description

The B119-4X4 is a 4x4 HDMI Matrix Switch that routes high-definition video from any four HDMI sources to any four HDMI displays. It supports video resolutions up to 1920 x 1200 (1080p) at 60 Hz. The 4x4 Matrix eliminates the need to disconnect and reconnect HDMI sources. It works with any HDMI source that connects to an HDMI display, and each source is accessible at all times by any display by selecting it with an IR remote or using the RS-232 port to switch the unit.

Features

- Share multiple HDMI sources between multiple monitors
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Switch between inputs via pushbuttons, remote control, or RS-232 serial
- Monitors can be located up to 25 ft. from the switch
- Supports video resolutions up to 1920 x 1200 (1080p) @ 60Hz
- HDCP and EDID compatible
- Mounting hardware included
- Plug-and-play; No software or drivers required
- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Share multiple HDMI sources between multiple monitors
- Supports video resolutions up to 1920 x 1200 (1080p) @ 60Hz
- Plug-and-play; No software or drivers required

Package Includes

- B119-4X4 Local Transmitter Unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A)
- 3.5 mm to DB9 Adapter Cable
- IR Extension Cable, 5 ft.
- Mounting Hardware
- Remote Control
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332180179
Product Type	Matrix Switch
Device Compatibility	Monitor/HDTV
Technology	HDMI; IR



Powering Business Worldwide

TRIPP LITE
SERIES

VIDEO	
Supported Resolutions	1920x1080 (1080p)
HDR Support	Yes
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5V / 3A
AC Power Adapter Cord Length (ft.)	4.0
AC Power Adapter Cord Length (m)	1.2
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	(4) HDMI (FEMALE)
Side B - Connector 1	(4) HDMI (FEMALE)
Input x Output	4 x 4
PHYSICAL	
Color	Black
Included Mounting Accessories	Yes
Rackmountable	No
Shipping Dimensions (hwd / in.)	2.10 x 6.30 x 13.70
Shipping Dimensions (hwd / cm)	5.33 x 16.00 x 34.80
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
Unit Dimensions (hwd / in.)	1.200 x 9.200 x 3.900
Unit Dimensions (hwd / cm)	3.05 x 23.37 x 9.91
Unit Weight (lbs.)	1.45
Unit Weight (kg)	0.66
COMMUNICATIONS	
Port Control	Push Buttons



Powering Business Worldwide

TRIPP LITE
SERIES

Signal Range (ft.)	60
Signal Range (m)	18
IP Remote Access	Yes
EDID Compatible	Yes
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA); CE (Europe); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B119-4X4](#)