

## Outdoor Full-Motion TV Wall Mount with Fully Articulating Arm for 32" to 80" Flat-Screen Displays

MODEL NUMBER: DWM3270XOUT



Mounts your 32 to 80 in. television to an outside wall to provide optimal viewing angles.

### Features

**Outdoor TV Wall Mount Positions Your Monitor at the Perfect Viewing Angle** This VESA-compliant full-motion TV wall mount lets you place your outdoor display signage or television where everyone can see it best. It's ideal for decks, balconies, patios, swimming pools, urgent care facilities, billboards, marquees, hotels, malls, theme parks, transportation hubs and anywhere else people watch a television set or monitor outdoors. It fits most flat-panel TVs from 37 to 80 inches and supports up to 110 pounds (50 kg).

**Swivel and Tilt the Screen to Find the Perfect and Most Comfortable Viewing Angle** The full-motion articulating arm adjusts independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -20° to +10° tilt and -90° to +90° swivel for positioning your screen just right. Easy -3° to +3° screen adjustment lets you quickly find just the right angle without interrupting your day.

**VESA-Compliant Mounting Ensures Display Compatibility** VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this TV wall mount supports the following VESA mounting hole patterns: 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300 and 400 x 400. Hardware for mounting on wood or concrete block is included.

**Sure to Stand Up Against Weather and Other Outdoor Elements** The weatherproof steel frame, high-grade powder-coated finish, stainless steel hardware and wall plate covers are specifically designed to withstand the stress of repeated adjustments and outdoor use. Monitor cables clip to the arm to eliminate clutter and keep your outdoor setting organized.

### Highlights

- TV wall mount with articulating arm adjusts viewing angle easily with just a single touch
- -20° to +10° tilt and -90° to +90° swivel helps you find the perfect angle to avoid glare
- Durable steel construction blends into any outdoor decor and supports up to 110 lb.
- Display cables attach to arm to reduce clutter and keep cords organized
- VESA compliance ensures compatibility with most popular mounting hole patterns

### Applications

- Mounting a flat-screen television or monitor outside an office building, bar, restaurant, mall or anywhere else outdoor digital signage is desired
- Installing a TV in your patio or pool area that can be easily adjusted to accommodate the comfort levels of the audience

### System Requirements

- Flat-screen television or monitor from 32 to 80 in.

### Package Includes

- Mount
- (2) Adapter brackets
- Hex wrench
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) D6 washers
- (4) D8 washers
- (8) Small spacers
- (8) Large spacers
- (4) Tapping screws
- (4) Concrete anchors
- (4) Washers
- Owner's manual

## Specifications



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332258786
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 300x200; 300x300; 400x200; 400x300; 400x400
Motion	Full
Mounting Location	Wall
Degrees of Motion	-20/+10 Tilt; 180 Swivel; -3/+3 Level Adjustment
Minimum Screen Size (in.)	32
Minimum Screen Size (cm)	81.2
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
Min/Max Arm Extension (in.)	4.57 min to 20.63 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	22.00 x 10.60 x 2.60
Shipping Dimensions (hwd / cm)	55.88 x 26.92 x 6.60
Shipping Weight (lbs.)	9.60
Shipping Weight (kg)	4.35
Unit Dimensions (hwd / in.)	18.900 x 16.900 x 8.600
Unit Dimensions (hwd / cm)	51.1 x 66 x 42.9
Unit Weight (lbs.)	8.4
Unit Weight (kg)	3.81
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Outdoor Use	Yes
STANDARDS & COMPLIANCE	

Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DWM3270XOUT](#)