



Powering Business Worldwide

pe.eaton.com

Double Row Terminal Block

TB200HB-18P

UPC:051712350198

Dimensions:

- **Height:** .75 IN
- **Length:** 2.51 IN
- **Width:** 1.37 IN

Weight: .5 LB

Warranties:

- Not Applicable

Specifications:

- **Special Features:** Breakdown voltage 4800V
- **Type:** High barrier
- **Amperage Rating:** 30A
- **Voltage Rating:** 600V
- **Center Spacing:** 0.437 in
- **Material:** Molded thermoplastic base, tin-plated brass terminal, P-style steel SEMS screw
- **Operating Temperature:** -40° to 130°C
- **Torque Rating:** 9 lb-in
- **Color:** Black
- **Number Of Poles:** 18-pole

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[TB200HB-18P](#)